

INSTRUCTIONS

CATERTRACT+™

MODELS: **CTT-LED-20S, CTT-LED-40S**

by **MECHLINE**

Thank you for purchasing the CATERTRACT+ LED glue board flying insect killer.

MODEL: **CTT-LED-20S**

FINISH: Stainless Steel

RANGE OF ACTION: 40Sq M

INPUT: 220V~240V /50Hz

POWER: 6W

LAMP TYPE: 1x6W E27 shatterproof

MODEL: **CTT-LED-40S**




FINISH: Stainless Steel

RANGE OF ACTION: 80Sq M

INPUT: 220V~240V /50Hz

POWER: 12W

LAMP TYPE: 2x6W E27 shatterproof



GENERAL: Mechline's CATERTRACT+ glue board flying insect killer utilises energy efficient, longlife LED lamps to lure light-sensitive flying insects, such as flies, moths, mosquitoes, etc. These insects are then trapped by the glue board which also contains an attractant. There are no chemicals, no smells, no sprays and no mess. The fly killer is pollution-free and harmless to humans and pets. Ideal for use in houses, factories, food outlets, cold rooms, hospitals and other places due to the shatterproof lamps. Indoor use only.



PRECAUTIONS

1. Disconnect power before repairing or cleaning.
2. Hang or mount in a safe place and away from children.
3. Keep away from flammable materials.
4. Check the voltage before operating. Confirm it is correct for the requirements of the fly killer.
5. If damaged, supply cords must be repaired or replaced by a qualified technician.
6. Clean the collection tray regularly.
7. Use caution when handling. Beware of possible sharp edges.

8. **Lamp(s) supplied with this unit have a clear plastic sheath around it which you should NOT attempt to remove. The sheath is integral to the lamp giving the shatterproof protection.**

9. **Lamps must be replaced after 13500 hours to ensure optimum performance of the fly killer.**
This is due to the natural deterioration of UV light intensity over this time.

10. Wall cladding without UV polymer stabilisers can discolour from UV degradation.



WARNING: This appliance is not intended for use by persons (including children) with reduced physical, sensory or mental capabilities or lack of experience and knowledge, unless they have been given supervision or instruction concerning use of the appliance by a person responsible for their safety.



MECHLINE DEVELOPMENTS LIMITED | Telephone: +44 (0)1908 261511 | Email: info@mechline.com | Web: www.mechline.com

INSTRUCTIONS

Rev: 12/2024

©2024 All rights reserved. All material on these pages, including and without limitation text, logos, icons, photographs and all other artwork, is cop right material of Mechline Developments Ltd, unless otherwise stated. Commercial use of this material may only be made with the express, prior, written permission of Mechline. This includes material provided by any third party, including material obtained through links to other sites from Mechline's pages or its affiliates and commercial associates. Material and information included are correct at time of print. Intending buyers and users must satisfy themselves as to the suitability and safety of the products for their particular purposes and duties. Dimensions shown in mm unless otherwise stated. Product accreditation may not apply to all products in the relevant range. Please contact Mechline to confirm. Unless otherwise stated, all products carry a warranty of twelve (12) months against manufacturing defect or workmanship on parts with no inclusion for labour or site attendance. (PEST-0012-b)