

Gram (UK) Limited 2 The Technology Centre, London Road, Swanley, Kent, BR8 7AG T: 01322 616900 F: 01322 616901 info@gramuk.co.uk

Innovative and functional food storage www.gram-commercial.com

Blast chill/freeze – it has never been easier

GRAM PROCESS KPS 21 and 42

KPS 21 and 42 are two new Gram blast chillers/freezers lines that feature innovative technological solutions offering high food safety and performance. With the new intuitive controller it has never been easier to manage chilling and freezing cycles.

Userfriendly and foodsafe

10

- Easy to read LCD control panel. The encoder wheel makes navigation intuitively easy to learn.
- Choose either the IFR operation, time or temperature controlled chill/freeze cycle.
- Prevent surface freezing damage with the IFR blast chilling function.
- HACCP alarms. If a power failure occurs or when a temperature limit is exceeded this will activate an audio-visual alarm.
- Up to 20 customised cycles can be stored.
- Operates as a storage cabinet after the chilling/freezing process has finished.

Chill

KPS 21 C and S: 22 kg from +70°C to 3°C in <u>90 min.</u>

KPS 42 C and S: 45 kg from +70°C to 3°C in 90 min.

Freeze KPS 21 S: 13 kg from +70°C to -18°C in 4 hours KPS 42 S:

KPS 42 S: 27 kg from +70°C to -18°C in 4 hours

: 0

GRAM







KPS 42

Dimensions in mm + legs KPS 21: 73-103, + legs KPS 42: 105-155



Hauptsitz: Hoshizaki Europe B.V.

Keienbergweg 50 C/D · 1101 GC Amsterdam · Niederlande T: +31 (0)20 6918499 · F: +31 (0)20 6918768 www.hoshizaki-europe.com · www.gram-commercial.com

UK Office :

2 The Technology Centre London Road · Swanley Kent BR8 7AG United Kingdom

T: +44 (0)845 456 0585 F: +44 (0)132 283 8331 uksales@hoshizaki.co.uk www.hoshizaki.co.uk

T: +44 (0)132 261 6900 F: +44 (0)132 261 6901 info@gramuk.co.uk www.gram-commercial.com



Intuitive and easy-to-use control panel

The bright LCD control panel is easy to

read. The encoder wheel makes

navigation intuitively easy.

Easy cleaning

The cabinets are fitted with an internal bottom tray with drain. Smooth surfaces and watertight internal rounded corners make cleaning easy. Removable support for 1/1 GN and 400 x 600 mm bakery plates.

		KPS 21 C	KPS 21 S	KPS 42 C	KPS 42 CR	KPS 42 S	KPS 42 SF
Blast chiller		1		1	1		
Blast chiller/freezer			1			\checkmark	1
Exterior/Interior	Stainless/Stainless	1	1	1	1	\checkmark	1
Compatible with oven rack	Rational oven rack type 101				1		1
Defrosting	Air	1	1	1	1	\checkmark	1
Exterior equipment	Right hand hinged door, reversible and selfclosing			•	•	•	•
	Right hand hinged door, reversible	•	•				
	Left hand hinged door	0	0	0	0	0	0
	Legs (H=73/103 mm)	•	•				
	Legs (H=105/155 mm)			•	•	•	•
Interior equipment	IFR control system	•	•	•	•	•	•
	Multipoint probe with 3 measuring points	•	٠	•	•	٠	•
	Removable support for 1/1 GN and 400 x 600 mm	•	٠	•	•	•	•
	Max. number of 1/1 GN 40 mm deep	5	5	10	10	10	10
	Cabinet fitted with an internal bottom tray	•	•	•	•	•	•
Prepared for remote refrigeration system				0	0	0	0

C = blast chiller

CR = blast chiller compatible with Rational oven rack type 101 \mathbf{CF} = blast chiller, prepared for remote refrigeration system

S = blast chiller/freezer

 \mathbf{SR} = blast chiller/freezer compatible with Rational oven rack type 101 SF = blast chiller/freezer, prepared for remote refrigeration system



IFR – Intelligent Food Recognition

Using the IFR function you only need to insert the multipoint probe and start the chilling cycle. The cycle then automatically adapts to the food item's characteristics.

Technical specifications		KPS 21 C	KPS 21 S	KPS 42 C	KPS 42 CF	KPS 42 S	KPS 42 SF	
With compressor		1	1	1		\checkmark		
Prepared for remote refrigeration system					1		1	
Temperature range	C°	0/+10	-25/+10	0/+10	0/+10	-25/+10	-25/+10	
Ref. capacity at -10/+45°C	Watt	1096	-	2631	2700	-	-	
Ref. capacity at -25/+45°C	Watt	-	870	-	-	2528	2600	
Connection	V/Hz	230/50	230/50	400/50	230/50	400/50	230/50	
Connection load	Watt	1000	1400	2200	274	4000	300	
Climate class		4	4	4	4	4	4	
Refrigerant	R404A							
Insulation, cyclopentane mm		55	55	75	75	75	75	
Weight, packed	Kg	130	125	225	185	225	185	

Temperature control modes

The chill/freeze cycle can be controlled by time or temperature. If the probe is not inserted into the core a time cycle will be activated automatically.